

375nm, 10mW, 1400mA, SMA Connector, Fiber-Coupled LED



Fiber Coupled LEDs

Stock **#23-727** 3-4 DAYS

⊖ 1 ⊕ **€850,00**

ADD TO CART

Qty 1+

€850,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
UV

Connector:
SMA

Current (mA):
1400 (maximum)

Operating Lifetime (hours):
~10,000

Output Power (mW):

10 (typical, with ø600µm Core Fiber)
Wavelength (nm): 375.00 (Nominal)
Contents of Kit: 1 x Mounted LED 1 x LED Driver 1 x SMA Cable for Modulation 1 x ø600µm, 1m Length, 0.22NA, MMIPatchcord
Note: 5V DC Power Supply sold separately
Bandwidth (nm): 12 (FWHM)
Forward Voltage (V) : 3.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
