

25mm Max. Aperture, Iris Diaphragm



Stock **#35-110** ☐ In Stock

-

1

+

€57,00

ADD TO CART

Qty 1-4
€57,00

Qty 5+
€50,40

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type: Unmounted
Minimum Aperture (mm): 0.8
Maximum Aperture (mm): 25.0
Outer Diameter (mm):

37.0
Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.90
Number of Leaves: 14.00
Thickness (mm): 5.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)