

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

38.1mm Dia., 3mm Thick, Uncoated, ISP Optics Magnesium Fluoride (MgF₂) Window | MF-W-38-3

See More by [ISP Optics](#)



Stock **#24-485** 3-4 DAYS



1



€400,00

ADD TO CART

Qty 1+

€400,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Abbe Number (v_d):
106.22

Bevel:
Protective as needed

Clear Aperture (%):
85

Clear Aperture CA (mm):

32.38
Diameter (mm): 38.10 +0.00/-0.13
Thickness (mm): 3.00 ±0.13
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 13.7
Density (g/cm³): 3.18
Edges: Fine Ground
Index of Refraction n_d: 1.377
Knoop Hardness (kg/mm²): 415
Parallelism (arcmin): <3
Poisson's Ratio: 0.271
Substrate: Magnesium Fluoride (MgF ₂)
Surface Flatness (P-V): 2λ
Surface Quality: 40-20
Type: Protective Window
Wavelength Range (nm): 120 - 7000
Young's Modulus (GPa): 138
Model Number: MF-W-38-3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View