

## TECHSPEC® 38.1mm Dia., 9.53mm Thick, N-BK7 Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock #38-058 [CONTACT US](#)

⊖ 1 ⊕

€185,00

ADD TO CART

Qty 1-5

€185,00

Qty 6+

€166,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Clear Aperture CA (mm):**  
34.29

**Coating:**  
Uncoated

**Diameter (mm):**  
38.10 +0.00/-0.10

**Substrate:**

[N-BK7](#)

**Index of Refraction  $n_d$ :**  
1.516

**Surface Quality:**  
10-5

**Thickness (mm):**  
9.53 ±0.20

**Type:**  
Laser Window Substrate

**Parallelism (arcmin):**  
<3

**Bevel:**  
Protective as needed

**Clear Aperture (%):**  
90

**Abbe Number ( $v_d$ ):**  
64.17

**Wavelength Range (nm):**  
350 - 2200

**Surface Flatness (P-V):**  
λ/10

**Edges:**  
Fine Ground

**Type of Window:**  
Glass

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 219:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)