

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #38-359-INK [CONTACT US](#)

[Other Coating Options](#)



1



€50,50

ADD TO CART

Qty 1-9

€50,50

Qty 10+

€45,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):

35.00 @ 587.6nm
Back Focal Length BFL (mm): 33.42
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.40 ±0.05
Edge Thickness ET (mm): 1.29
Radius R₁ (mm): 18.09
Clear Aperture CA (mm): 11.5
f/#: 2.8
Numerical Aperture NA: 0.18
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View