

38.4mm Diameter x 30mm FL, PCX Condenser Lens



Stock **#43-594** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€45,00**

ADD TO CART

Qty 1-10
€45,00

Qty 11+
€40,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
38.40 +0.2/-0.4

Effective Focal Length EFL (mm):
30.00

Numerical Aperture NA:
0.64

Substrate: B270
Focal Length Tolerance (%) : ±7
Coating: Uncoated
Centering (arcmin) : ≤25
Surface Quality: 80-50 (typical)
Center Thickness CT (mm) : 19.00 ±0.25
f# : 0.78
Bevel: Protective bevel as needed
Radius R₂ (mm) : 84.125
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm) : 350 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View