

3.9mm CA, A-39N0-P16 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series - 6 pins FPC with Thermistor



3.9mm CA, A-39N0-P16 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series - 6 pins FPC with Thermistor



Stock **#15-740** CLEARANCE ☐ In Stock

- 1 +

€112,95

ADD TO CART

Qty 1+

€112,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.50

Coating:
VS

Type: Packaged Lens w/ Thermistor
Clear Aperture CA (mm): 3.9
Contents of Kit: Packaged A-39N0 with a straight flex cable with thermistor FPC-A-16 (6 pins)
Focus Range: -5 to +15 diopter
Model Number: A-39N0-P16
Operating Temperature (°C): -20 to +60
Storage Temperature (°C): -40 to +85
Thickness (mm): 5.20
Transmission (%): 97 @ 587nm
Transmitted Wavefront Error, RMS: 50nm
Typical Applications: Industrial vision, medical imaging cameras, optical equipment, & biometric devices requiring a large clear aperture

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
