

TECHSPEC® 3" Dia, 6" FL Uncoated, Spherical Mirror



Stock #32-826 3-4 DAYS

- 1 + **€191,00**

ADD TO CART

Qty 1-9
€191,00

Qty 10+
€162,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy: λ/4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 6.00
Effective Focal Length EFL (mm): 152.40
Radius of Curvature (mm): 304.80
Aperture (f/#): f/2
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View