

4" x 4" White Advanced Illumination Collimated Backlight

See More by [Advanced Illumination](#)



Advanced Illumination Side-Fired Collimated LED Backlight

Stock **#36-469** 3-4 DAYS



1



€831,00

ADD TO CART

Qty 1+

€831,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Model Number:
CX0404-WHIIC

Operating Temperature (°C):
0 - 60

Dimensions (mm):
166.6 L x 166.6 W x 19.1 T

LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (inches): 4 x 4
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)