

4.0 OD M30.5 x 0.50, Machine Vision Absorptive ND Filter



Stock **#21-773** [CONTACT US](#)

- 1 + **€106,00**

ADD TO CART

Qty 1-9
€106,00

Qty 10+
€101,80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
25.50

Filter Thread:
M30.5 x 0.50

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
