

TECHSPEC® 400-700nm OD 0.6, M30.5 x 0.5 Absorptive ND Filter



Stock **#66-720** [CONTACT US](#)

- 1 + **€78,00**

ADD TO CART

Qty 1-9
€78,00
Qty 10+
€72,80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm): 33.50
Optical Density OD (Average): 0.6
Clear Aperture CA (mm): 22.0
Filter Thread:

M30.5 x 0.50
Substrate: ND Filter Glass
Coating: Uncoated
Transmission (%): 25.00
Type: Neutral Density Filter
Stock No. of Unmounted Filter: #46-214
Mount Thickness (mm): 9.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View