

40° Travel, 60 x 60mm Stage Size Metric Goniometer, R63



Stock #55-840 3-4 DAYS

⊖ 1 ⊕

€782,00

ADD TO CART

Qty 1-4
€782,00

Qty 5+
€703,80

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Guide System:
Dovetail

Type of Drive:
Lead Screw

Type:

Metric
Stage Size (mm): 60 x 60
Travel (°): ±20
Construction: Brass Stage
Load Capacity (kg): 5
Mounting Threads: (1) M6 x 1.0, (8) M4 x 0.7
Radius R (mm): 63
Resolution (°): 0.1
Weight (kg): 1.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant