

40mm Dia. x 4mm MgF₂ Coated, N-BK7 Window



Stock **#27-855** CLEARANCE 3-4 DAYS

- 1 + **€14,95**

ADD TO CART

Qty 1+
€14,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Abbe Number (v_d): 64.17
Bevel: Protective as needed
Clear Aperture CA (mm): 36.00
Diameter (mm): 40.00 ±0.25
Thickness (mm): 4.00 ±0.20

Coating: MgF ₂ (400-700nm)
Coating Specification: MgF ₂ : ¼λ @ 550nm, R _{avg} ≤ 1.75% @ 400 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): ≤5
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Accuracy: 1λ
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 82

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View