

TECHSPEC®

4.0mm Dia. x 8.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#47-863** ☐ In Stock
[Other Coating Options](#)

-

1

+

€58,00

ADD TO CART

Qty 1-9
€58,00
Qty 10+
€52,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.00 +0.0/-0.025

Effective Focal Length EFL (mm):

8.00 @ 587.6nm
Back Focal Length BFL (mm): 7.17
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BAF10
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.39 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 5.36
Clear Aperture CA (mm): 3.6
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant