

TECHSPEC® 40mm, Side Drive, Standard Top, English, Micrometer Stage



40mm, Side Drive, Standard Top

Stock **#66-406** [CONTACT US](#)



1



€358,00

ADD TO CART

Qty 1-2

€358,00

Qty 3+

€312,10

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation: Side Drive
Type: English
Stage Size (mm): 40 x 40
Travel (inches): 0.5
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 4
Mounting Threads: (1) 1/4-20, (4) 6-32, (8) 2-56
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)