

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



High Performance Off-Axis Parabolic Mirrors

Stock #90-977 [CONTACT US](#)



1



€1.395,00

ADD TO CART

Qty 1-9

€1.395,00

Qty 10+

€1.256,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Dimensions (mm):
40.0 x 40.0

Dimensional Tolerance (mm):

+0.0/-0.2
Effective Focal Length EFL (mm): 209.00
Radius of Curvature (mm): 418.00
Coating: Bare Aluminum
Coating Type: Metal
Coating Specification: R _{abs} >85% @ 250 - 700nm
Off-Set Angle (°): 24
Parent Focal Length PFL (mm): 200.0
Clear Aperture (%): 90.00
Surface Accuracy: λ/4
Surface Quality: 80-50
Center Thickness CT (mm): 16.00
Center Thickness Tolerance (mm): ±0.2
Parent Focal Length Tolerance (mm): ±0.5%
Substrate: Float Glass
Y Offset Tolerance (mm): ±2.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View