

[See all 3 Products in Family](#)

40X Deluxe Illuminated Direct Measuring Microscope



Stock #55-678 **10 In Stock**

- 1 + €555.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€555,00 each
Qty 5+	€527,60 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type of Illumination:
Adjustable & removable, battery operated

Type of Focusing:
Rack and Pinion

Note:
Magnification includes 10XEyepiece

Physical & Mechanical Properties

4.5 **Field of View (mm):**

0.02mm/0.001" **Increments:**

200.00 **Height (mm):**

0 - 3 **Reticle Scale (mm):**

0 - 0.10 **Reticle Scale (inches):**

580.00 **Weight (g):**

Optical Properties

40X **Magnification:**

15.0 **Working Distance (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

Reticle cannot and should not be removed or replaced.

- 40X and 100X Models, Include 10X Eyepiece
- Inch/Metric Reticle
- Rack and Pinion Focusing

For quick and precise measurements in laboratories, workshops and assembly lines. Features a dual scale reticle graduated in both inches and millimeters. A turn of the eyepiece brings the reticle into sharp focus. Vertical adjustment knob sharpens the subject image. Includes a fully vertically adjustable battery operated penlight illuminator, which can be removed for use elsewhere. Scope has cutaway opening at base for subject manipulation.

Note: Reticle cannot and should not be removed or replaced.