

## 41 x 63.5mm AR Coated Float Glass Window



Stock #32-740 **13 In Stock**

€27<sup>25</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€27,25 each
Qty 6-49	€24,00 each
Qty 50-99	€23,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Protective Window **Type:**

Glass **Type of Window:**

### Physical & Mechanical Properties

41.00 x 63.50 **Dimensions (mm):**

3.00 (nominal)	<b>Thickness (mm):</b>
63.50	<b>Length (mm):</b>
41.00	<b>Width (mm):</b>
Fine Ground	<b>Edges:</b>

## Optical Properties

BBAR (400-700nm)	<b>Coating:</b>
Float Glass	<b>Substrate:</b> □
80-50	<b>Surface Quality:</b>
400 - 700	<b>Wavelength Range (nm):</b>
4 - 6λ	<b>Surface Flatness (P-V):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

## Compatible Mounts

;