

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Multi-Band Fluorescence Bandpass Filters

Stock #87-239 3-4 DAYS



1



€383,00

ADD TO CART

Qty 1-9

€383,00

Qty 10+

€318,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

12.50 +0.0/-0.1

Angle of Incidence (°):

0

Bandwidth (nm):

40 @ 440nm

21 @ 521nm 34 @ 607nm 45 @ 700nm
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 8.81
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Transmission (%): >90
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Mounted in Black Anodized Ring
Compatible Fluorophore: DAPI/FITC/TRITC/CY5 Emission
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.00 ±0.25
Multi-Band Center Wavelengths (nm): 440, 521, 607, 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant