

45 x 35° Diffusing Angle, 25mm Dia., Mounted Flat Top Holographic Diffuser



Flat Top Holographic Diffusers

Stock **#15-831** CLEARANCE 3-4 DAYS

⊖ 1 ⊕

€195,00

ADD TO CART

Qty 1+

€195,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diffusing Angle (°):
45 x 35 (FWHM)

Clear Aperture CA (mm):
21.6

Diameter (mm):
25.00 ±1

Operating Temperature (°C):
-30 to +100 (Maximum of 240 Hours)

Substrate: ☐
Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Flat Top Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant