

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 45° AOI, 50.0mm Square, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock #64-471 3-4 DAYS



1



€98,00

ADD TO CART

Qty 1-9

€98,00

Qty 10+

€86,20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):  
45

Coating:  
Hot Mirror, 45°

Substrate:   
BOROFLOAT®

|                                                                                                                                                      |
|------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Dimensions (mm):</b><br>50.0 x 50.0                                                                                                               |
| <b>Surface Quality:</b><br>80-50                                                                                                                     |
| <b>Thickness (mm):</b><br>3.30                                                                                                                       |
| <b>Thickness Tolerance (mm):</b><br>±0.2                                                                                                             |
| <b>Type:</b><br>Dichroic Filter                                                                                                                      |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2                                                                                                      |
| <b>Coating Specification:</b><br>T <sub>avg</sub> >85% @ 400 - 690nm, R <sub>avg</sub> >95% @ 750 - 1125nm<br>AR: R <sub>avg</sub> <1% @ 400 - 700nm |
| <b>Wavelength Range (nm):</b><br>400 - 1125                                                                                                          |
| <b>Surface Flatness (P-V):</b><br>4 - 6λ                                                                                                             |
| <b>Coating Type:</b><br>Dielectric                                                                                                                   |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |