

TECHSPEC® 45° Plate Beamsplitter Mount



45° Plate Beamsplitter Mount, #85-699

Stock #85-699 [CONTACT US](#)

⊖ 1 ⊕ €58⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€58,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed **Function:**
Elliptical **Type of Optics:**

Physical & Mechanical Properties

25.0 **Compatible Plate Inner Diameter (mm):**
Clear Aperture CA (mm):

12.5

Black Anodized Aluminum

Construction:

25.0

Dimensions (mm):

Threading & Mounting

25.0 - 35.36

Size of Compatible Optics (mm):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[Compliant](#)

Reach 224:

[View](#)

Certificate of Conformance:

Product Details

- Interchangeable to Quickly Swap Optics
- Plate and Cube Beamsplitter Mount Options
- Anodized Aluminum Construction
- [Adjustable Optical Mounts](#) Also Available

Designed to fit within the inner diameter of 25mm and 30mm standard [cage system plates](#), TECHSPEC® Cage System Fixed Optical Mounts are ideal for mounting beamsplitters and additional optical components. The [#85-699](#) 45° Plate Beamsplitter Mount can also fit within [#85-695](#) 25.4mm Kinematic Mount. Additionally, Cube Beamsplitter Mounts can be connected to [cage system tubes](#) utilizing the tubes' M23.2 x 0.75 threaded inner diameter.