

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

4mm Aperture UV/VIS Fiber Optic Collimator, FC



4mm Aperture Fiber Optic Collimator, FC

Stock #88-189 3-4 DAYS



1



€220,00

ADD TO CART

Qty 1-10

€220,00

Qty 11+

€194,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.35

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Type:
Fiber Collimator

Wavelength Range (nm): 190 - 1250
Aperture Size: 4.0
Compatible Fiber NA: 0.22
Connector: FC
Fiber Diameter (µm): compatible up to 400
Focal Length FL (mm): 10.00
Housing Material: Stainless Steel
Length (mm): 19.70
Note: No Compatible Refocusing Assemblies
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
