

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

4" X 4" (1000 lp/inch), Ronchi Ruling



Stock #58-460 3-4 DAYS



1



€977,00

ADD TO CART

Qty 1-4

€977,00

Qty 5+

€929,10

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Substrate:
Float Glass

Optical Density OD (Average):

3.00
Dimensions (inches): 4 x4
Surface Quality: 60-40
Thickness (mm): 1.50
Type: English
Parallelism (arcmin): ±60
Dimensional Tolerance (mm): ± 0.02
Frequency (lp/inch): 1000.00
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View