

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50.0mm 193nm 45°, Excimer Laser Line Mirror



TECHSPEC Excimer Laser Line Mirrors

Stock #48-931 3-4 DAYS



1



€380,00

ADD TO CART

Qty 1-5
€380,00

Qty 6+
€335,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):

<3
Clear Aperture (%):>90
Back Surface:Ground
Reflection at DWL (%):97
Coating Specification:R_{abs} >97% @ 193nm
Surface Flatness (P-V):λ/10
Coating Type:Dielectric
Coating:Dielectric Mirror (193nm)
Design Wavelength DWL (nm):193
Diameter (mm):50.00 +0.0/-0.2
Thickness (mm):10.00 ±0.2
Angle of Incidence (°):45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, By Design: 1.5 J/cm² @ 10ns

Regulatory Compliance

RoHS:Compliant
Certificate of Conformance:View