

50/50.8mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts



50/50.8mm Diameter Kinematic Mount, 3-Screws , #58-855



Stock **#17-524** [CONTACT US](#)



1



€192,30

ADD TO CART

Qty 1+

€192,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
50.0 - 50.8

Number of Adjustment Screws:

Clear Aperture CA (mm):
45.9

Travel (mm):
Z-Axis: 12

Construction:
Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings

Angle Tolerance (°):
0.2 per 0.25mm turn

Fine Tilt Angle (°):
±5

Fine Tip Angle (°):
±5

Sensitivity per 1° Knob Rotation (arcsec):
2.3

Thermal Stability (μrad):
<5

Adjustment Screw Pitch (mm):
0.25

Contents of Kit:
[#58-855](#), [#15-857](#), [#15-845](#)

Compatible Post:
M4 x0.7, 8-32

Min. Thickness of Compatible Optics (mm):
2.0

Pointing Stability (μrad):
1.3

Optical Axis Height (mm):
127.00

Post Diameter (mm):
25.4

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 224:
[Compliant](#)

Certificate of Conformance:
[View](#)