

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50/50.8mm Sq. Hoya/SCHOTT Complete Colored Glass Longpass Filter Kit (37 Filters)

See More by [Hoya](#)



Stock #17-017 [CONTACT US](#)



1



€1.885,00

ADD TO CART

Qty 1+

€1.885,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
SCHOTT: 50.0 x 50.0
Hoya: 50.8 x 50.8

Substrate: ☐
Colored Glass

Filters Included :
[SCHOTT N-WG280](#), [SCHOTT N-WG295](#), [SCHOTT N-WG305](#), [SCHOTT N-WG320](#), [Hoya L-37](#), [SCHOTT GG395](#), [SCHOTT GG400](#), [SCHOTT GG420](#), [SCHOTT GG435](#), [SCHOTT GG455](#), [SCHOTT GG475](#), [SCHOTT](#)

[GG495](#), [Hoya Y-50](#), [SCHOTT OG515](#), [SCHOTT OG530](#), [Hoya O-54](#), [SCHOTT OG550](#), [Hoya O-56](#), [SCHOTT OG570](#), [Hoya L-38](#), [SCHOTT OG590](#), [Hoya R-60](#), [SCHOTT RG610](#), [Hoya R-62](#), [SCHOTT RG630](#), [SCHOTT RG645](#), [Hoya R-66](#), [SCHOTT RG665](#), [SCHOTT RG695](#), [SCHOTT RG715](#), [Hoya R-72](#), [Hoya IR-76](#), [SCHOTT RG780](#), [Hoya IR-80](#), [SCHOTT RG830](#), [SCHOTT RG850](#), [SCHOTT RG1000](#)

Coating:

Uncoated

Color:

Multiple Colors

Type:

Longpass Filter

Wavelength:

UV-NIR

Bevel:

Protective as needed

Regulatory Compliance

RoHS:

[Compliant](#)

Certificate of Conformance:

[View](#)