

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50.0/50.8mm Optic Diameter, X-Y Translating Optic Mount, Quick Start Optical Mounts



#17-534 and #17-513



Stock #17-514 [CONTACT US](#)

- 1 +

€322,70

ADD TO CART

Qty 1+

€322,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Linear (XY)

Type of Optics:
Circular

Size of Compatible Optics (mm):
50.0 - 50.8

Clear Aperture CA (mm):

46.0
Thickness of Compatible Optics (mm): 15.0 (Max)
Outer Diameter (mm): 88.0
Thickness (mm): 22.00
Travel (mm): ±2.0 in X and Y
Weight (g): 180
Construction: Black Anodized Aluminum
Contents of Kit: #62-957 , #16-317 , #15-849
Compatible Post: M6 x 1.0
Optical Axis Height (mm): 127.00
Post Diameter (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
