

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25mm Max. Aperture, Mounted Iris Diaphragm



50.8mm Outer Diameter, Mounted Iris Diaphragm, #53-915

Stock #53-915 3-4 DAYS



1



€72,00

ADD TO CART

Qty 1-4

€72,00

Qty 5+

€63,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Mounted

Minimum Aperture (mm):
0.8

Maximum Aperture (mm):
25.0

Outer Diameter (mm): 50.8
Construction: Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators, Black Anodized Aluminum Mount
Inner Diameter (mm): 37.00
Lever Diameter (mm): 3.00
Lever Length (mm): 12.90
Mounting Threads: 1/4-20
Set Screw Thread: 6-32
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)

