

**TECHSPEC® 50mm 532nm, Laser Line Polarizing Cube Beamsplitter**



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-862** 3-4 DAYS



1



€615,00

ADD TO CART

Qty 1-5

€615,00

Qty 6+

€484,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Beam Deviation (arcmin):**  
±3

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
90.00

|                                                                                |
|--------------------------------------------------------------------------------|
| <div>Coating Specification:</div> <div>R<sub>abs</sub> &lt;0.25% @ 532nm</div> |
| <div>Construction:</div> <div>Cube</div>                                       |
| <div>Design Wavelength DWL (nm):</div> <div>532</div>                          |
| <div>Dimensions (mm):</div> <div>50.0 x 50.0 x 50.0 ±0.1</div>                 |
| <div>Extinction Ratio:</div> <div>1000:1</div>                                 |
| <div>P-Polarization Transmission (%):</div> <div>&gt;95</div>                  |
| <div>S-Polarization Reflection (%):</div> <div>&gt;99.5</div>                  |
| <div>Substrate: <div><div></div></div></div> <div>N-BK7</div>                  |
| <div>Surface Flatness (P-V):</div> <div>λ/4</div>                              |
| <div>Surface Quality:</div> <div>40-20</div>                                   |
| <div>Type:</div> <div>Linear Polarizer</div>                                   |

## Regulatory Compliance

|                                                        |
|--------------------------------------------------------|
| <div>RoHS 2015:</div> <div>Compliant</div>             |
| <div>Reach 219:</div> <div>Compliant</div>             |
| <div>Certificate of Conformance:</div> <div>View</div> |