

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm, Aluminum & MgF₂ Coated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #45-397 3-4 DAYS



1



€231,00

ADD TO CART

Qty 1-5

€231,00

Qty 6+

€207,90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

MgF₂ & Aluminized

Substrate: ☐

[N-BK7](#)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 70.70
Length of Legs (mm): 50.00
Image Orientation: Left-Handed
Coating Specification: Hypotenuse: R _{avg} >85% @ 400 - 700nm Legs: R _{avg} ≤1.75% @ 400 - 700nm
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/4
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns Legs: 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View