


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Calcium Fluoride (CaF2) Windows

Stock #22-609 3-4 DAYS



1



€302,50

ADD TO CART

Qty 1-10

€302,50

Qty 11+

€272,25

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
94.99

Axis Orientation:
Random

Bevel:

Protective as needed
Clear Aperture (%) : 90
Clear Aperture CA (mm) : 45.00
Diameter (mm) : 50.00 +0.0/-0.1
Thickness (mm) : 1.00 ±0.1
Coating : UV-VIS (250-700nm)
Coating Specification : R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 18.85
Density (g/cm³) : 3.18
Edges : Fine Ground
Index of Refraction n_d : 1.434
Knoop Hardness (kg/mm²) : 158.3
Parallelism (arcmin) : <1
Poisson's Ratio : 0.26
Substrate : Calcium Fluoride (CaF ₂) Vacuum UV Grade
Surface Flatness (P-V) : 2λ
Surface Quality : 40-20
Type : Protective Window
Wavelength Range (nm) : 250 - 700
Young's Modulus (GPa) : 75.8
Damage Threshold, By Design : ☐ 3 J/cm² @ 355nm, 10ns 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant