

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

50mm Dia. Broadband IR Laser Mirror



Stock #33-001 3-4 DAYS



1



€431,00

ADD TO CART

Qty 1-5

€431,00

Qty 6+

€380,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
20-10

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

90
Coating Specification: R_{avg} >98.8% @ 2 - 20µm
Wavelength Range (nm): 2000 - 20000
Surface Flatness (P-V): λ/20 @ 10.6µm
Coating Type: Metal
Coating: Bare Gold
Diameter (mm): 50.00 +0.00/-0.12
Thickness (mm): 10.00 ±0.15
Substrate: ☐ Copper
Surface Roughness (Angstroms): <50 RMS
Damage Threshold, By Design: ☐ Typical: 50 kW/cm²

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View