

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-646 □ In Stock



1



€165,00

ADD TO CART

Qty 1-9

€165,00

Qty 10+

€149,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Diameter (mm):

50.00

Extinction Ratio:

9000:1 @ 546nm

Substrate: XP42 Laminated Between Glass
Operating Temperature (°C): -10 to +55
Thickness (mm): 2.00 ±0.10
Transmission (%): 42 @ 546nm
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.00/-0.20
Construction: Laminated Glass Polarizing Film
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98 @ 546nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant