

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50mm Dia. X 100mm FL, Uncoated Germanium Meniscus Lens



Stock #87-960 3-4 DAYS



1



€931,00

ADD TO CART

Qty 1-5

€931,00

Qty 6+

€744,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
100.00

Substrate: ☐
Germanium (Ge)

f/#:

2.00
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Back Focal Length BFL (mm): 96.49
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Edge Thickness ET (mm): 3.8
Focal Length Specification Wavelength (μm): 10.6
Radius R ₁ (mm): 107.03
Radius R ₂ (mm): 160.46
Surface Quality: 60-40
Wavelength Range (μm): 2 - 14

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View