

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 5.0mm Dia. X 30.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock #88-636-INK [CONTACT US](#)

[Other Coating Options](#)

1 **€58,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €58,50                        |
| Qty 10+                       |
| €52,75                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
5.00 ±0.025

Effective Focal Length EFL (mm):

|                                                                                                   |
|---------------------------------------------------------------------------------------------------|
| 30.00 @ 587.6nm                                                                                   |
| <b>Back Focal Length BFL (mm):</b><br>28.95                                                       |
| <b>Coating:</b><br>VIS-EXT (350-700nm)                                                            |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <0.5% @ 350 - 700nm                             |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                               |
| <b>Surface Quality:</b><br>40-20                                                                  |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                             |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                       |
| <b>Focal Length Tolerance (%):</b><br>±1                                                          |
| <b>Centering (arcmin):</b><br><1                                                                  |
| <b>Center Thickness CT (mm):</b><br>1.60 ±0.05                                                    |
| <b>Edge Thickness ET (mm):</b><br>1.40                                                            |
| <b>Radius R<sub>1</sub> (mm):</b><br>15.50                                                        |
| <b>Clear Aperture CA (mm):</b><br>4.5                                                             |
| <b>f/#:</b><br>6                                                                                  |
| <b>Numerical Aperture NA:</b><br>0.08                                                             |
| <b>Type:</b><br>Plano-Convex Lens                                                                 |
| <b>Bevel:</b><br>Protective bevel as needed                                                       |
| <b>Wavelength Range (nm):</b><br>350 - 700                                                        |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm <sup>2</sup> @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |