

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm Dia. X 50mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock #45-905-INK [CONTACT US](#)

- 1 + **€82,50**

ADD TO CART

Qty 1-9
€82,50
Qty 10+
€74,25
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Back Focal Length BFL (mm):
45.30

Effective Focal Length EFL (mm): 50.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 16.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 7.39
Radius R₁=R₂ (mm): 74.78
Clear Aperture CA (mm): 49.00
f/#: 1.00
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View