

TECHSPEC® 50mm Dia. x 75mm FL, Uncoated Germanium Meniscus Lens



Stock **#87-959** 3-4 DAYS

⊖ 1 ⊕ **€931,00**

ADD TO CART

Qty 1-5
€931,00
Qty 6+
€744,80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
Germanium (Ge)

f/#:

1.5
Numerical Aperture NA: 0.33
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Back Focal Length BFL (mm): 71.56
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Edge Thickness ET (mm): 3.5
Focal Length Specification Wavelength (μm): 10.6
Radius R ₁ (mm): 81.89
Radius R ₂ (mm): 122.77
Surface Quality: 60-40
Wavelength Range (μm): 2 - 14

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View