

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Convex Mirrors

Stock #87-662 3-4 DAYS



1



€63,00

ADD TO CART

Qty 1-5

€63,00

Qty 6+

€50,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-50.00

Center Thickness CT (mm):
5.00

Clear Aperture (%): 90.00
Coating: Protected Aluminum (400-700nm)
Coating Specification: R_{avg} >85% @ 400 - 700nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.83
Focal Length Tolerance (%): ±2
Radius R (mm): 100.0
Substrate: ☐ N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant