

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm Dia X -50mm FL, Protected Silver, Convex Mirror



Convex Mirrors

Stock #87-684 3-4 DAYS

1 €78,00

ADD TO CART

Qty 1-5

€78,00

Qty 6+

€62,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-50.00

Center Thickness CT (mm):
5.00

Clear Aperture (%) : 90.00
Coating : Protected Silver (450-10000nm)
Coating Specification : R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating Type : Metal
Dimensional Tolerance (mm) : +0.0/-0.1
Edge Thickness ET (mm) : 1.83
Focal Length Tolerance (%) : ±2
Radius R (mm) : 100.0
Substrate : ☐ N-BK7
Surface Accuracy : λ/2
Surface Quality : 60-40
Thickness Tolerance (mm) : ±0.1
Type : Spherical Mirror
Wavelength Range (nm) : 500 - 10000

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant