


50mm Diameter Narrow Circular Holographic Diffuser Kit



Holographic Diffusers



Stock **#48-012** [CONTACT US](#)

- 1 +

€802,50

ADD TO CART

Qty 1+

€802,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diffusing Angle (°):
0.5, 1, 5, 10

Diameter (mm):
50.00 ±0.1

Number of Diffusers:
4.00

Operating Temperature (°C):

-30 to +100 (Maximum of 240 Hours)

Substrate: ☐
Polycarbonate

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
