

50mm Diameter x 44mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-541** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€57,00**

ADD TO CART

Qty 1-10
€57,00
Qty 11+
€50,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.2/-0.4

Effective Focal Length EFL (mm):
44.00

Numerical Aperture NA:
0.57

Substrate: B270
Focal Length Tolerance (%) : ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin) : ≤25
Surface Quality: 80-50 (typical)
Center Thickness CT (mm) : 18.80 ±0.25
f/#: 0.88
Bevel: Protective bevel as needed
Radius R₂ (mm) : Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm) : 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant