

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm Diameter X -100 FL, NIR II Coated, Plano-Concave Lens



Stock #68-003 3-4 DAYS

[Other Coating Options](#)

1 €65,00

ADD TO CART

Qty 1-9
€65,00
Qty 10+
€58,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-100.00
Substrate: N-BK7
f#: 2.00
Coating: NIR II (750-1550nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -103.3
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 49.00
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 11.23
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Radius R₁ (mm): -51.68
Surface Quality: 40-20
Damage Threshold, Reference: 8 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant