

TECHSPEC® 50mm H x 25mm L x 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-199** 3-4 DAYS

- 1 + **€110,00**

ADD TO CART

Qty 1-5
€110,00
Qty 6+
€88,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate:
[N-BK7](#)

f/#:
2

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 94.93
Center Thickness CT (mm): 7.70
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 50.0 x 25.0
Edge Thickness ET (mm): 1.28
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View