

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



MegaPixel Fixed Focal Length Lenses

Stock #56-790 3-4 DAYS

[Similar Products](#)



1



€300,00

ADD TO CART

Qty 1+

€300,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
63.00

Iris Option:
Variable

Length (mm):
38.10

Horizontal Field of View, 1/2" Sensor:
7.60°

Filter Thread: M30.5 x0.50
Maximum Diameter (mm): 33.50
Weight (g): 85.00
Maximum Rear Protrusion (mm): 0.90
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 50.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 500 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View