

TECHSPEC® 50mm VIS, 50R/50T, Non-Polarizing In-Line Cube Beamsplitter



Stock **#20-098** 3-4 DAYS

⊖ 1 ⊕ **€655,00**

ADD TO CART

Qty 1-5
€655,00

Qty 6+
€557,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VS
Coating Specification: R_{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 50.0 x 50.0 x 50.0
Note: Absorptive Surface Treatment on Blackened Face
Reflection/Transmission Ratio (R/T): 50/50
Substrate: N-BK7
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
Ts-Tp : <6%
Absolute Transmission (%): 45 ±10
Average Transmission (%): 45 ±5
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant