

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #57-090 3-4 DAYS

1 €149,00

ADD TO CART

Qty 1-4

€149,00

Qty 5+

€131,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Acceptance Angle (°):
25.4

Buffer Material:
Polyimide

Cladding Diameter (µm):

125 +1/-3
Coating: VS/NIR
Minimum Bend Radius (mm): 25/13 (Continuous/Momentary)
Substrate:  Fused Silica (Corning 7980)
Length (m): 25.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 145 ±5
Core Diameter (µm): 50 ±2
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.440
Wavelength Range (nm): 300 - 2400
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View