

50mW, 405nm Fiber-Coupled Laser Module



Stock #19-477 3-4 DAYS

- 1 + **€700,00**

ADD TO CART

Qty 1-9
€700,00
Qty 10+
€625,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
+15 to +30

Operating Voltage (V):
5.0

Output Power (mW):

50
Spatial Mode: Fiber-Coupled
Wavelength (nm): 405.00 ±5
Length of Fiber (m): 1
Type of Laser: Diode
Laser Class - CDRH: Class IIIb
Color: Violet
Connector: SMA
Length (mm): 151.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant