

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #21-837 3-4 DAYS



1



€2.665,00

ADD TO CART

Qty 1+

€2.665,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Blue

Input Voltage (V):
24

Model Number:
LFV3-G-50BL

Dimensions (mm):
W 60 mm x D 84 mm x H 57 mm

Wavelength (nm):
470.00

Weight (g): 285
Power Consumption (W): 15
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-733 China: #66-855
Active Area (mm): 52 mm x 52 mm
Type of Illumination: LED Illuminator
Manufacturer: CCS
Geometry: Coaxial Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View