

TECHSPEC®

51mm Dia. UV Enhanced Aluminum, λ/4 Mirror



Stock **#46-720** 3-4 DAYS

-

1

+

€105,00

ADD TO CART

Qty 1-5
€105,00
Qty 6+
€84,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
51.00

Surface Flatness (P-V):
λ/4

Substrate: BOROFLOAT®

Back Surface: Fine Ground
Surface Quality: 60-40
Dimensional Tolerance (mm): +0.5/-0.0
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 13.00 +1.0/-0.0
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant